

Product data sheet

Characteristics

EZM31600TB

Main unit, EZ Meter-Pak, 1600A,
208Y/120VAC, 3 phase, 4 wire, 1200A Al/Cu
busbar, main lugs terminal box, over/under



Main

Range of product	EZ meter-pak
Product or component type	Meter center main unit
Main type	Main Lugs
Included Items	Box

Complementary

Main rated current	1600 A
Bus rated current	1200 A
Material	Aluminium/copper busbar
Enclosure material	Steel
[Ue] rated operational voltage	208Y/120 V AC 240/120 V delta AC
Device mounting	Surface
Number of Phases	3 phase in 3 phase out
Service feed location	UG OH
Electrical connection	Lugs 1 AWG 6...300 kcmil aluminium/copper) ground Lugs 6 AWG 3/0...600 kcmil aluminium/copper) line Lugs 6 AWG 3/0...600 kcmil aluminium/copper) neutral
Wiring configuration	4-wire
Height	55.09 in (1399.29 mm)
Width	22.48 in (570.99 mm)
Depth	13.00 in (330.20 mm)

Environment

Product certifications	UL Listed
Enclosure Rating	NEMA 3R

Ordering and shipping details

Category	00020 - EZ METER-PAK
Discount Schedule	DE4
GTIN	00785901515944
Nbr. of units in pkg.	1
Package weight(Lbs)	165 lb(US) (74.84 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	1.22 ft (0.373 m)
Package 1 width	2.13 ft (0.648 m)
Package 1 Length	4.67 ft (1.422 m)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------