



Main

Product or component type	Circuit breaker
---------------------------	-----------------

Complementary

Number of Poles	3P
Breaking capacity code	D
Magnetic hold current	1125 A
Magnetic tripping current	2250 A
Electrical connection	Plug-in line Plug-in load
Tightening torque	230.12 lbf.in (26 N.m) 0.15...0.29 in ² (95...185 mm ²) (AWG 3/0...350 kcmil)
Height	8 in (203.20 mm)
Width	4.12 in (104.65 mm)
Depth	12.72 in (323.09 mm)
Continuous current rating	80 %

Ordering and shipping details

Category	01110-HD,JD UNIT MT BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901448891
Package weight(Lbs)	7.73 lb(US) (3.506 kg)
Returnability	No
Country of origin	US

Packing Units

Package 1 Height	5.20 in (13.208 cm)
Package 1 width	11.00 in (27.940 cm)
Package 1 Length	14.50 in (36.830 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------