

# 9422TC33

Operating mechanism, flange mounted, variable depth, 30A, 600 V, replacement fuse clips, for H, K, J, R fuses



## Main

Range	9422T
Product	Disconnect Switch
Disconnect Type	Fusible disconnect switch

## Complementary

Current Rating	30 A
Horsepower Rating	7.5 Hp 200 V AC 7.5 Hp 230 V AC 15 Hp 460 V AC 20 Hp 575 V AC 5 hp 250 V DC
Fuse Rating	60 A 250 V 30 A 600 V
Handle Type	Ordered separately
Fuse Type	R K H J

## Environment

Certifications	CSA UL Recognized
----------------	----------------------

## Ordering and shipping details

Category	21732 - 9422
Discount Schedule	CP1
GTIN	00785901858454
Nbr. of units in pkg.	1
Package weight(Lbs)	1.03 lb(US) (0.47 kg)
Returnability	No
Country of origin	MX

## Packing Units

Package 1 Height	4.30 in (10.922 cm)
Package 1 width	6.00 in (15.240 cm)
Package 1 Length	6.70 in (17.018 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------