



Main

Range	Thalassa
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Device application	Multi-purpose
Enclosure nominal dimensions	-
Mounting location	Step slide Back inserts
Mounting plate description	Plain
Range compatibility	Thalassa PLA
Device composition	1 mounting plate
Material	Galvanised steel

Complementary

Fixing mode	By screws M8 - on back inserts
Permanent permissible load	330.69 lb(US) (150 kg)
Height	Nominal 59.06 in (1500 mm) Real 54.72 in (1390 mm)
Width	Nominal 39.37 in (1000 mm) Real 34.45 in (875 mm)
Depth	Real 4.92 in (125 mm)
Thickness	0.98 in (25 mm)

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	00785901320777
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.51 in (1.3 cm)
Package 1 width	38.78 in (98.5 cm)
Package 1 Length	54.13 in (137.5 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------