



Main

Range	Linergy
Product name	FT
Device short name	GV1G
Product or component type	Flexible connection
Accessory / separate part category	Connection accessory
Range compatibility	TeSys GV2 TeSys D

Complementary

Product compatibility	LC1D09...D38
Poles description	3P
[Ie] rated operational current	25 A
Quantity per set	Set of 10
Net Weight	0.03 lb(US) (0.013 kg)

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901874065
Nbr. of units in pkg.	1
Package weight(Lbs)	0.03 lb(US) (0.01 kg)
Returnability	Yes
Country of origin	TN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.38 in (3.5 cm)
Package 1 width	3.54 in (9 cm)
Package 1 Length	4.72 in (12 cm)
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Weight	4.09 oz (116 g)
Package 2 Height	1.57 in (4 cm)
Package 2 width	3.54 in (9 cm)
Package 2 Length	4.72 in (12 cm)
Unit Type of Package 3	S01
Number of Units in Package 3	250
Package 3 Weight	6.80 lb(US) (3.085 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------