



### Main

Range of product	Lineryg
Product or component type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of packing	String of bags
Quantity per set	10 sets of 100
Cable cross section	0.00 in <sup>2</sup> (1.5 mm <sup>2</sup> )

### Complementary

Cable end type	Single conductor
Additional information	With integrated marker tag holder
Color	Black
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG gauge	AWG 16
Bezel size	Ø 4 mm
Tube diameter	0.08 in (2 mm)
Length	0.55 in (14 mm)
Tube length	0.31 in (8 mm)
CAD overall depth	1.26 in (32 mm)
Net Weight	0.40 lb(US) (0.18 kg)

### Environment

Product certifications	UL
Ambient air temperature for operation	-4...221 °F (-20...105 °C)

### Ordering and shipping details

Category	22621 - IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	00785901535522
Nbr. of units in pkg.	1000
Package weight(Lbs)	0.01 lb(US) (0.00 kg)
Returnability	No
Country of origin	DE

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.20 in (0.5 cm)
Package 1 width	0.20 in (0.5 cm)
Package 1 Length	1.18 in (3 cm)
Unit Type of Package 2	BAG
Number of Units in Package 2	100

Package 2 Weight	0.60 oz (17 g)
Package 2 Height	0.59 in (1.5 cm)
Package 2 width	1.38 in (3.5 cm)
Package 2 Length	2.36 in (6 cm)
Unit Type of Package 3	BB1
Number of Units in Package 3	1000
Package 3 Weight	6.56 oz (186 g)
Package 3 Height	3.15 in (8 cm)
Package 3 width	3.54 in (9 cm)
Package 3 Length	4.72 in (12 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Halogen free product

### Contractual warranty

Warranty	18 months
----------	-----------