



### Main

Range	Thalassa
Product name	Thalassa TBP
Device application	Multi-purpose
Category	Industrial box
Height	7.56 in (192 mm)
Width	4.76 in (121 mm)
Depth	3.43 in (87 mm)
Internal height	6.89 in (175 mm)
Internal width	4.13 in (105 mm)
Internal depth	3.15 in (80 mm)
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Quantity per set	Set of 2
Body type	One piece moulded
Type of front cover	Low plain cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

### Complementary

Material	polycarbonate
Color	Grey (RAL 7035)
Standards	IEC 62208 UL 508 A
Product certifications	TÜV UL
Electrical insulation class	Class II
Mounting location	Outdoor
Net Weight	0.74 lb(US) (0.335 kg)

### Environment

IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK08 conforming to IEC 62262
Fire resistance	1760 °F (960 °C)
Ambient air temperature for storage	5...140 °F (-15...60 °C)
Operating temperature	-13...176 °F (-25...80 °C)

### Ordering and shipping details

Category	80033 - ENCLOSURE SYSTEMS POLYESTER
Discount Schedule	ES1
GTIN	00785901685463
Nbr. of units in pkg.	2
Package weight(Lbs)	1.41 lb(US) (0.64 kg)
Returnability	Yes
Country of origin	HU

## Packing Units

Package 1 Height	3.43 in (87.000 mm)
Package 1 width	4.76 in (121.000 mm)
Package 1 Length	7.56 in (192.000 mm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------