



Main

Product or component type	Circuit breaker
---------------------------	-----------------

Complementary

Number of Poles	3P
Breaking capacity code	D
Magnetic hold current	875 A
Magnetic tripping current	1750 A
Electrical connection	I-Line connection line Lugs load
Tightening torque	230.12 lbf.in (26 N.m) 0.04...0.15 in ² (25...95 mm ²) (AWG 4...AWG 4/0)
Phase connection	ABC
Height	11.48 in (291.59 mm)
Width	4.48 in (113.79 mm)
Depth	5.87 in (149.10 mm)
Continuous current rating	80 %

Ordering and shipping details

Category	01112 - HD, JD I-LINE BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901700678
Nbr. of units in pkg.	1
Package weight(Lbs)	9.45 lb(US) (4.29 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	6.20 in (15.748 cm)
Package 1 width	8.50 in (21.59 cm)
Package 1 Length	15.00 in (38.1 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------