

AC617

17 MIL PREMIUM DUCT TAPE 'Bottom Board'

DESCRIPTION

Polyethylene (PE) coated cloth tape with an aggressive pressure-sensitive natural rubber adhesive adheres well to a wide variety of surfaces under a wide range of temperature conditions. Designed to meet demanding applications. Easy dispensing from roll.

PRODUCT APPLICATION

For temporary patching of utility access holes, taping of ductwork, and a variety of heavy-duty demanding applications requiring high strength and adhesion.

GOVERNMENT CONFORMANCE

Tested in accordance with UL-723.

INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

NOMINAL VALUES

The following data are nominal values based on PSTC, ASTM and other standard tests. The data should not be considered as specifications.

Backing	PE Film
Adhesive	Natural Rubber/Resin
Reinforcement	PET Cloth
Adhesion to Steel (oz/in of width) PSTC-101	60 (16.4 N/25mm)
Tensile Strength (lbs/in of width) PSTC-131	44 (193 N/25mm)
Elongation (% at break) PSTC-131	12
Total Thickness (mils) PSTC-133	17.0 (.432mm)
Color	Black
Temperature Resistance	+32°F ~ +200°F (+0°C ~ +93°C)



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA

Customer Service: 800.IPG.8273 | 800.474.8273

Tape Technical Service: 877.447.4832

www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 03/20

