



## Main

|                             |                      |
|-----------------------------|----------------------|
| Panelboard Type             | Main lugs            |
| Product or component type   | Interiors            |
| Branch Circuit Breaker Type | QOB<br>QOB-VH<br>QHB |
| Busbar Material             | Copper               |

## Complementary

|                                |  |
|--------------------------------|--|
| Number of spaces               | 72   |
| Enclosure Nominal Height       | 44 in (1117.60 mm)   |
| Enclosure Nominal Width        | 20 in (508.00 mm)  |
| Enclosure Nominal Depth        | 5.75 in (146.05 mm) NEMA 1<br>6.5 in (165.10 mm) NEMA 3R/5/12  |
| Line Rated Current             | 225 A  |
| [Iu] rated interrupted current | 10 KA<br>22 KA<br>65 kA  |
| Wiring configuration           | 3-wire   |
| Number of Phases               | 1 phase  |
| Voltage Rating                 | 240 V AC<br>48 V DC  |
| Tightening torque              | 40.01...50.01 Lbf.In (4.52...5.65 N.m) 0.02...0.10 in <sup>2</sup> (13.30...67.43 mm <sup>2</sup> ) (AWG 6...AWG 2/0)<br>100.01 Lbf.In (11.3 N.m) 0.02...0.10 in <sup>2</sup> (13.30...67.43 mm <sup>2</sup> ) (AWG 6...AWG 2/0)<br>274.99 Lbf.In (31.07 N.m) 0.02...0.27 in <sup>2</sup> (13.30...177.3 mm <sup>2</sup> ) (AWG 6...350 kcmil)<br>274.99 Lbf.In (31.07 N.m) 0.02...0.20 in <sup>2</sup> (13.30...126.7 mm <sup>2</sup> ) (AWG 6...250 kcmil)<br>274.99 lbf.in (31.07 N.m) 0.17...0.24 in <sup>2</sup> (107.2...152 mm <sup>2</sup> ) (AWG 4...300 kcmil) |
| Height                         | 39 in (990.60 mm)  |
| Width                          | 10.44 in (265.18 mm)   |

## Environment

|           |           |
|-----------|-----------|
| Standards | UL<br>CSA |
|-----------|-----------|

## Ordering and shipping details

|                       |                            |
|-----------------------|----------------------------|
| Category              | 09151 - NQ RTA PANELBOARDS |
| Discount Schedule     | PE1A                       |
| GTIN                  | 00785901856320             |
| Nbr. of units in pkg. | 1                          |
| Package weight(Lbs)   | 26.12 lb(US) (11.85 kg)    |
| Returnability         | Yes                        |
| Country of origin     | MX                         |

## Packing Units

|                  |                   |
|------------------|-------------------|
| Package 1 Height | 0.54 ft (0.165 m) |
| Package 1 width  | 1.17 ft (0.356 m) |
| Package 1 Length | 3.67 ft (1.118 m) |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|