

SC1624M100F

Homeline All In One combination service entrance device, semi flush, ringed socket, no bypass, OH, UG, 100 A, 16 spaces



Main

Product or component type	All-In-One
Range of product	Homeline
Meter socket type	Ringed
Hub type	B300 A

Complementary

Line Rated Current	100 A
Short-circuit current	10 kA
Mounting	Semi flush
Number of spaces	16
Number of circuits	24
Number of Tandem Breakers	8
Electrical connection	Lugs line side Lugs service ground
Wire Size	AWG 6...AWG 2/0 aluminium)line side AWG 6...AWG 2/0 copper)line side AWG 6...AWG 2/0 aluminium)service ground AWG 6...AWG 2/0 copper)service ground
Tightening torque	Main lugs: 50 lb.in, AWG 6...AWG 2/0, aluminium/copper Service ground 50 lb.in, AWG 6...AWG 2/0, aluminium/copper Branch lugs 35 lb.in, AWG 6...AWG 4, aluminium/copper Branch lugs 25 lb.in, AWG 8, aluminium/copper Branch lugs 20 lb.in, AWG 14...AWG 10, aluminium/copper Branch lugs 20 lb.in, AWG 12...AWG 10, aluminium/copper Cover 10 lb.in
Disconnect	Service disconnect (factory installed)
Disconnect Rating	100 A
Branch Breaker Rating	100 A
Service feed location	OH UG
Bypass type	No bypass
Width	14.50 in (368.30 mm)
Depth	3.39 in (86.11 mm)
Height	25.12 in (638.05 mm)

Ordering and shipping details

Category	00148 - HOMELINE CSED DEVICES
Discount Schedule	DE3A
GTIN	00785901107798
Nbr. of units in pkg.	1
Package weight(Lbs)	38 lb(US) (17.24 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	7.60 in (19.304 cm)
Package 1 width	17.20 in (43.688 cm)
Package 1 Length	27.20 in (69.088 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------