

# Product data sheet

## Characteristics

# 8538SCG34V02S

NEMA Combination Starter, Type S, 30A  
fusible disconnect, Size 1, 27A, 10 HP at 600  
VAC polyphase, 120 VAC coil, NEMA 1



### Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

### Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	10 Hp 460 V AC, 3 phase 10 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3
Disconnect Type	Fusible disconnect switch R, 30 A
NEMA size	1

### Environment

Enclosure Type	NEMA 1 painted sheet steel with external reset
----------------	--

### Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901021261
Nbr. of units in pkg.	1
Package weight(Lbs)	30.73 lb(US) (13.94 kg)
Returnability	No
Country of origin	MX

### Packing Units

Package 1 Height	11.10 in (28.194 cm)
Package 1 width	10.50 in (26.670 cm)
Package 1 Length	27.20 in (69.088 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------