

Product data sheet

Characteristics

2510FW2P

Manual Starter, fractional horsepower, 16A, 2 poles, 1 HP at 277 VAC, red indicator, NEMA 4 enclosure, 2 conduit opening



Main

Product	Single Unit Manual Starter
Type	F
Overload Relay Type	Melting alloy

Complementary

Current Rating	16 A
Cable entry	0.75 NPT (bottom)
Horsepower Rating	1 Hp 115 V AC 1 Hp 277 V AC 0.75 Hp 115 V DC 0.75 Hp 230 V DC 2 hp 230 V AC
Voltage Rating	277 V AC 230 V DC
Number of Poles	2P
Control Unit	Toggle switch (with lock-off)
Number of Phases	1 phase
Pilot Light	Red indicator
Reset	Manual
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 12 copper
Height	4.38 in (111.25 mm)
Width	3 in (76.20 mm)
Depth	4.56 in (115.82 mm)

Environment

Product certifications	UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
NEMA Enclosure Rating	NEMA 4 die cast zinc alloy standard size

Ordering and shipping details

Category	21101 - 2510,2511,2512 F
Discount Schedule	CP1
GTIN	00785901554387
Nbr. of units in pkg.	1
Package weight(Lbs)	2.99 lb(US) (1.36 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	3.60 in (9.144 cm)
Package 1 width	4.50 in (11.430 cm)
Package 1 Length	5.40 in (13.716 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------