



## Main

Range	9422T
Product	Disconnect Switch
Disconnect Type	Fusible disconnect switch

## Complementary

Mounting Type	Flange rod variable depth
Current Rating	400 A
Horsepower Rating	75 Hp 200 V AC 125 Hp 230 V AC 250 Hp 460 V AC 350 Hp 575 V AC 50 hp 250 V DC
Fuse Rating	400 A 250/600 V
Handle Type	Ordered separately
Fuse Type	R K J H

## Environment

Certifications	UL Recognized CSA
----------------	----------------------

## Ordering and shipping details

Category	21732 - 9422
Discount Schedule	CP1
GTIN	00785901728412
Nbr. of units in pkg.	1
Package weight(Lbs)	67.4 lb(US) (30.57 kg)
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	9.00 in (22.86 cm)
Package 1 width	14.60 in (37.084 cm)
Package 1 Length	25.70 in (65.278 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------