



Overview

Lead time	Usually Ships within 4 Weeks
-----------	------------------------------

Main

Range	Spacial
Accessory / separate part category	Enclosure accessory
Product or component type	Plinth front
Anwendung	PC application Electronic application Multi-purpose Compartmentalised application
Nennmaße des Gehäuses	-
Device composition	Fixing elements 4 corner cover 1 front panel 1 rear panel 4 corner
Range compatibility	Spacial SF Spacial SM Spacial SD Spacial S3D Spacial CRN
Mounting support	Plinth side panels

Complementary

Fixing mode	By fixing element - on structure location
Color	Gray RAL 7022)
Surface finish	Epoxy-polyester powder
Permanent permissible load	2866.01 lb(US) (1300 kg)
Height	3.94 in (100 mm)
Width	Nominal 23.62 in (600 mm)

Environment

IP degree of protection	IP30 (complete plinth)
IK degree of protection	IK10

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	03606485126562
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	TN

Packing Units

Package 1 Height	4.33 in (110.000 mm)
Package 1 width	7.87 in (200.000 mm)
Package 1 Length	24.21 in (615.000 mm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------