



Main

| | |
|------------------------------------|----------------------|
| Range | Acti 9 |
| Product or component type | Comb busbar |
| Accessory / separate part category | Connection accessory |
| Lines description | 3L |
| Length in 18 mm modules | 57 |

Complementary

| | |
|--------------------------------|--|
| Number of ways | 19 ways 3 L |
| Poles configuration for 1 way | 1 x 3P |
| Connection pitch | 0.71 in (18 mm) |
| Connector type | Tooth |
| Distance between way | 2.13 in (54 mm) |
| Marking | L1 L2 L3 |
| Insulation | Insulated |
| Device presentation | Cuttable |
| Provided equipment | Set of 10 end piece |
| [Ie] rated operational current | 100 A 104 °F (40 °C) |
| [Ue] rated operational voltage | 415 V AC |
| [Ui] rated insulation voltage | 500 V AC IEC 61439-2 |
| Mounting mode | Horizontal |
| Mounting location | Top or bottom tunnel type terminals Top or bottom on double terminal |
| 9 mm pitches | 114 |
| Height | 39.37 in (1000 mm) |
| Color | White (RAL 9003) |
| Range compatibility | Acti 9 iC60 Acti 9 iK60 Acti 9 iID Acti 9 iID K Acti 9 iSW Acti 9 iSW-NA Multi 9 C60 |

Environment

| | |
|-------------------------|---------------------------------------|
| Standards | IEC 60947-7-1 IEC 61439-2 |
| Fire resistance | 1760 °F (960 °C) 30 s) IEC 60695-2-1 |
| Pollution degree | 3 conforming to IEC 60947-7-1 |
| IP degree of protection | IP20 with end-pieces and tooth covers |

Ordering and shipping details

| | |
|-----------------------|-----------------------|
| Category | 01078 - DE2 MISC |
| Discount Schedule | DE2 |
| GTIN | 00785901511700 |
| Nbr. of units in pkg. | 5 |
| Package weight(Lbs) | 1.24 lb(US) (0.56 kg) |
| Returnability | No |
| Country of origin | DE |

Packing Units

| | |
|------------------------------|----------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 2.17 in (5.5 cm) |
| Package 1 width | 3.54 in (9 cm) |
| Package 1 Length | 42.24 in (107.3 cm) |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 5 |
| Package 2 Weight | 6.81 lb(US) (3.09 kg) |
| Package 2 Height | 2.17 in (5.5 cm) |
| Package 2 width | 42.24 in (107.3 cm) |
| Package 2 Length | 3.54 in (9 cm) |
| Unit Type of Package 3 | P12 |
| Number of Units in Package 3 | 270 |
| Package 3 Weight | 394.56 lb(US) (178.968 kg) |
| Package 3 Height | 44.09 in (112 cm) |
| Package 3 width | 31.50 in (80 cm) |
| Package 3 Length | 47.24 in (120 cm) |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|