

PG29

LOW TACK PREMIUM PAPER MASKING TAPE

DESCRIPTION

A beige, fine crepe paper masking tape with a low tack, pressure-sensitive synthetic rubber/resin adhesive and non-printable rubber release coat. Smooth-to-the-touch and easy to work with. Resists paint flaking upon removal and provides straight, clean paint-break line.

PRODUCT APPLICATION

Interior masking, (i.e. walls, woodwork and windows) for new home construction and home improvement. General purpose masking and protective masking. Can also be used for wet strip automotive paint masking.



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA
Customer Service: 800.IPG.8273 | 800.474.8273
Tape Technical Service: 877.447.4832
www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 02/11

INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

NOMINAL VALUES

The following data are nominal values based on PSTC, ASTM and other standard tests. The data should not be considered as specifications.

Backing	Fine Crepe Paper
Adhesive	Synthetic Rubber/resin
Adhesion to Steel (oz/in of width) PSTC-101	25 (6.8 N/25mm)
Tensile Strength (lbs/in of width) PSTC-131	25 (109 N/25mm)
Elongation (% at break) PSTC-131	10
Total Thickness (mils) PSTC-133	6.8 (0.17mm)
Quick Stick (oz/in of width) PSTC-5	
To Kraft	3 (0.8 N/25mm)
To Steel	13 (3.6 N/25mm)
Color	Beige

