

Product data sheet

Characteristics

8903SVG2V02

Contacteur, Type S, multipole lighting, electrically held, 200A, 3 pole, 110/120VAC 50/60Hz coil, NEMA 1



Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	200 A
Number of Poles	3P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical connection	Lugs
Height	39.13 in (994 mm)
Depth	10.24 in (260 mm)
Width	22.17 in (563 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product certifications	UL Listed CSA

Ordering and shipping details

Category	21325 - 8903 S (NOT S°C) ELECT.
Discount Schedule	CP1
GTIN	00785901625988
Nbr. of units in pkg.	1
Package weight(Lbs)	114 lb(US) (51.71 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	0.96 ft (0.292 m)
Package 1 width	2.07 ft (0.630 m)
Package 1 Length	3.62 ft (1.102 m)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------