

HOM220EPD

Mini circuit breaker, Homeline, 20A, 2 pole, 120/240 VAC, 10 kA AIR, ground fault class B, plug in mount



Main

| | |
|------------------------------|---------------------------------------|
| Product | Miniature circuit-breaker |
| Range | Homeline |
| Current Rating | 20 A |
| Certifications | UL Listed |
| Voltage Rating | 120/240 V AC |
| Mounting Type | Plug-in |
| Number of Poles | 2P |
| Short Circuit Current Rating | 10 kA |
| Number of Spaces | 2 |
| Circuit Breaker Type | Ground fault protecting class B 30 mA |
| Ratings | HACR rated |
| Electrical Connection | Screw clamp terminals |
| Wire Size | AWG 14...AWG 8 aluminium/copper)1 |

Complementary

| | |
|-------------------|---|
| Tightening torque | 40.71 Lbf.in (4.6 N.m) 0.00...0.02 in ² (2.5...10 mm ²) (AWG 16...AWG 14) 40.71 lbf.in (4.6 N.m) 0.01...0.03 in ² (4...20 mm ²) (AWG 12...AWG 4) |
|-------------------|---|

Environment

| | |
|---------------------------------------|----------------|
| Ambient air temperature for operation | 104 °F (40 °C) |
|---------------------------------------|----------------|

Ordering and shipping details

| | |
|-----------------------|---------------------------------|
| Category | 00143 - HOM 1 & 2P EPD BREAKERS |
| Discount Schedule | DE3D |
| GTIN | 00785901564300 |
| Nbr. of units in pkg. | 33 |
| Package weight(Lbs) | 33 lb(US) (14.97 kg) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------|---------------------|
| Package 1 Height | 2.20 in (5.588 cm) |
| Package 1 width | 3.40 in (8.636 cm) |
| Package 1 Length | 5.30 in (13.462 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |

| | |
|-----------------------------|---|
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
| Halogen content performance | Halogen free product |

Contractual warranty

| | |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|
