



Main

Product or component type	Circuit breaker
---------------------------	-----------------

Complementary

Number of Poles	3P
Breaking capacity code	D
Magnetic hold current	750 A
Magnetic tripping current	1500 A
Electrical connection	I-Line connection line Lugs load
Tightening torque	230.12 lbf.in (26 N.m) 0.04...0.15 in ² (25...95 mm ²) (AWG 4...AWG 4/0)
Phase connection	ABC
Height	11.48 in (291.59 mm)
Width	4.48 in (113.79 mm)
Depth	5.87 in (149.10 mm)
Continuous current rating	80 %

Ordering and shipping details

Category	01112 - HD, JD I-LINE BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901558422
Nbr. of units in pkg.	1
Package weight(Lbs)	6.82 lb(US) (3.09 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	5.80 in (14.732 cm)
Package 1 width	8.60 in (21.844 cm)
Package 1 Length	14.80 in (37.592 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------