



Main

| | |
|-------------------|-------------------------|
| Product | Surge protection device |
| Range | Surgelogic |
| Device Short Name | EMA |

Complementary

| | |
|---------------------------|---|
| Surge Current | 160 kA |
| Voltage Rating | 208Y/120 V AC |
| Number of Phases | 3 phase |
| Wiring Configuration | 4-wire |
| Connection | Lugs AWG 10...AWG 2 copper 35.40 lbf.in (4 N.m) |
| MCOV | 150 V |
| Nominal Discharge Current | 20 kA |
| SCCR | 200 kA |
| Local Signalling | Status LED green per phase normal operation Status LED red per phase fault |
| Provided Equipment | Alarm enable/disable switch Surge counter Dry contacts |
| Device Mounting | Surface |
| Height | 11.10 in (282 mm) |
| Width | 9.98 in (253.5 mm) |
| Depth | 5.31 in (135 mm) |
| Cable length | 19.02 in (483 mm) |

Environment

| | |
|--------------------|--|
| Enclosure Rating | NEMA 1 |
| Enclosure Material | Gray painted sheet steel |
| Standards | CSA C22.2 No 8 UL 1449:ed. 4 UL 1283:ed. 5 |
| Ambient Operating | 149 °F (65 °C) |

Ordering and shipping details

| | |
|-----------------------|------------------------------|
| Category | 08464 - SURGE PROTECTION EMA |
| Discount Schedule | DE1B |
| GTIN | 00785901781653 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 15.77 lb(US) (7.15 kg) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------|----------------------|
| Package 1 Height | 6.00 in (15.240 cm) |
| Package 1 width | 13.50 in (34.290 cm) |
| Package 1 Length | 12.00 in (30.480 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |