HSM Pure 220

Personal shredder

More Data protection at your home or small office





- Personal/home office model designed for 1 to 3 users
- High quality materials and "Made in Germany" quality for security and durability
- Cutting rollers made of hardened steel with lifetime warranty
- Quiet operation minimizes noise development in the workplace
- Low power consumption in standby mode
- Paper feed with overload protection reduces paper jams
- Automatically switches off if pressure is applied to the safety element
- Practical automatic start/stop
- Full bag indicator
- Effortless emptying of the waste container via the removable housing top
- Timeless machine design in trendy white
- Uses an 11 gallon capacity shred bag; Part #HSM1310











HSM Part#	HSM2320	HSM2323
Cutting type	Strip cut	Cross cut
Cutting size	1/8"	5/32" x 1"
Security level DIN 32757-1	2	3
Security level DIN 66399	P-2 / T-2 / E-2	P-4 / T-4 / E-3 / F-1
Cutting capacity per run in sheets	13 - 15	7 - 8
Cutting Speed	8.6 ft / min	8.6 ft / min
Throat opening	9"	9"
Motor power (horsepower)	0.4 hp	0.4 hp
Voltage	115 V / 60Hz	115 V / 60Hz
Dimensions (H x W x D)	18.3" × 14.4" × 10.1"	18.3" x 14.4" x 10.1"
Weight	8.8 lbs	9.9 lbs
Shred-bin volume	5.3 gal	5.3 gal
Cutting capabilities		

All technical specifications are approximate values. Technical and design modifications reserved.

