



Main

Product	Circuit breaker
Range	QO
Current Rating	100 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Bolt-on
Number of Poles	2P
Ratings	Primary main breaker
Electrical Connection	Lugs
Frame Size	QOM2

Complementary

Interrupt Rating	22 kA 120/240 V AC 50/60 Hz 22 kA 120 V AC 50/60 Hz
Wire Size	AWG 4...300 kcmil copper or aluminium
Tightening Torque	53.10 lbf.in (6 N.m) 0.01...0.10 in ² (4...65 mm ²) (AWG 12...AWG 2/0)
Height	5.6 in (142.24 mm)
Width	5.07 in (128.78 mm)
Depth	3.6 in (91.44 mm)
Load Center Type	Main breaker
Number of Phases	1 phase
For Use With	QO load center

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00024 - Q2 & QE METERING BREAKERS
Discount Schedule	DE2A
GTIN	00785901301509
Nbr. of units in pkg.	1
Package weight(Lbs)	2.6 lb(US) (1.18 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	4.30 in (10.922 cm)
Package 1 width	5.50 in (13.970 cm)
Package 1 Length	6.50 in (16.510 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------