


# Product data sheet

## Characteristics

# 9050AO20EV02

Timing Relay, Type A, pneumatic, on delay, 0.1 to 60 seconds, 10A, 600 V, DPDT, timed, 110/120 VAC 50/60 Hz coil, open



### Main

Product range	9050A/H
Product type	Timer
Timing Mode	On-delay
Timing Range	0.1 s...1 min
Switch Function	DPDT
Coil Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Contact Operation	Time delayed 2 NO + 2 NC
Current rating	10 A

### Complementary

Maximum switching voltage	600 V AC
Electrical connection	Screw-clamp terminals
Reset response time	29 Ms - on-delay 27 ms - off-delay
Mounting Support	Panel

### Environment

Ambient Temperature Range - Operational	68...104 °F (20...40 °C)
Certifications	UL Listed CSA
Height	2.64 in (67 mm)
Width	4.02 in (102 mm)
Depth	4.37 in (111 mm)

### Ordering and shipping details

Category	21631 - 9050 A ONE MINUTE PNEUMATIC TIMER
Discount Schedule	CP1
GTIN	00785901866626
Nbr. of units in pkg.	1
Package weight(Lbs)	1.7 lb(US) (0.77 kg)
Returnability	No
Country of origin	MX

### Packing Units

Package 1 Height	25.40 in (64.516 cm)
Package 1 width	10.00 in (25.400 cm)
Package 1 Length	64.52 in (163.871 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------