



Main

Range compatibility	Harmony XAC
Accessory / separate part type	Incandescent bulb
Accessory / separate part category	Lighting accessory
Accessory / separate part destination	Illuminated push-button
[Us] rated supply voltage	130 V AC/DC
Signalling colour	Clear
Sale per indivisible quantity	10

Complementary

Power dissipation in W	2.4 W
Bulb base	BA 9s
Diameter	0.39 in (10 mm)
Length	1.10 in (28 mm)

Ordering and shipping details

Category	22466 - PUSHBUTTON, ACCESSORIES
Discount Schedule	CS2
GTIN	00785901263739
Nbr. of units in pkg.	10
Package weight(Lbs)	0.01 lb(US) (0.00 kg)
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.38 in (3.5 cm)
Package 1 width	1.77 in (4.5 cm)
Package 1 Length	4.13 in (10.5 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	1.13 oz (32 g)
Package 2 Height	1.38 in (3.5 cm)
Package 2 width	1.77 in (4.5 cm)
Package 2 Length	4.13 in (10.5 cm)
Unit Type of Package 3	S02
Number of Units in Package 3	800
Package 3 Weight	6.32 lb(US) (2.868 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------