



Main

Range of product	Harmony 9001K
Product or component type	Complete control station
Device short name	KY
Provided equipment	Contact block Legend plate
Contact block name	KA1

Complementary

Enclosure/cubicle description	Surface mounting
Enclosure material	Stainless Steel
Type of installation	Indoor/outdoor
Control station composition	2 push-buttons 1 NO + 2 NC START-STOP
Connections - terminals	Screw-clamp terminals
[Ie] rated operational current AC	10 A

Environment

NEMA degree of protection	NEMA 3/4/13
---------------------------	-------------


Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901040149
Nbr. of units in pkg.	1
Package weight(Lbs)	3.62 lb(US) (1.64 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	10.16 in (25.806 cm)
Package 1 width	4.00 in (10.160 cm)
Package 1 Length	25.81 in (65.548 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------