



Main

Product line	QO
Product type	Load Center Grounding Bar Assembly

Complementary

Number of connectors	21
Wire size	AWG 14...AWG 4 copper AWG 12...AWG 4 aluminium AWG 6...AWG 3/0 aluminium/copper
Provided equipment	2 screw
Bar length	5.87 In (149 mm) 5.87 in (149 mm)
Maximum length of segment	3.15 In (80 mm) 5.24 in (133 mm)
Device mounting	Direct mounting back of enclosure
Height	0.437 in (11.10 mm)
Depth	0.312 in (7.92 mm)
Tightening torque	30 lb.in 20 lb.in, AWG 14...AWG 10, copper 20 lb.in, AWG 12...AWG 10, aluminium 35 lb.in, AWG 6...AWG 4 25 lb.in, AWG 8 25 lb.in, AWG 14...AWG 12, copper 25 lb.in, AWG 12...AWG 10, aluminium

Ordering and shipping details

Category	00102 - QO LC ACCESSORIES
Discount Schedule	DE3A
GTIN	00785901328162
Nbr. of units in pkg.	5
Package weight(Lbs)	0.4 lb(US) (0.18 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	0.80 in (2.032 cm)
Package 1 width	2.00 in (5.080 cm)
Package 1 Length	5.80 in (14.732 cm)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------