



Main

Product	Single Throw Safety Switch
Duty Rating	Light duty
Device application	Furnace Garages
Disconnect Type	Fusible disconnect
Factory Installed Neutral	Neutral (factory installed)
Phase	3 phase
Number of Poles	1
Current Rating	30 A
Voltage Rating	120 V AC
NEMA degree of protection	NEMA 1

Complementary

Short-circuit current	10 kA
Fuse Type	Plug
Mounting Type	Surface
Wiring configuration	2-wire
Wire Size	AWG 14...AWG 8 copper AWG 12...AWG 8 aluminium
Tightening torque	30 Lbf.In (3.39 N.m) 0.00...0.01 in ² (2.082...8.367 mm ²) (AWG 14...AWG 8) 30 lbf.in (3.39 N.m) 0.01...0.01 in ² (3.307...8.367 mm ²) (AWG 12...AWG 8)
Depth	4 in (101.60 mm)
Width	6.13 in (155.70 mm)
Height	7.63 in (193.80 mm)

Ordering and shipping details

Category	00057 - LIGHT DUTY SW, NEMA1, 30A
Discount Schedule	DE1A
GTIN	00785901115489
Nbr. of units in pkg.	1
Package weight(Lbs)	3.34 lb(US) (1.51 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.50 in (13.97 cm)
Package 1 width	6.40 in (16.256 cm)
Package 1 Length	8.60 in (21.844 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	200
Package 2 Weight	678.00 lb(US) (307.535 kg)
Package 2 Height	40.00 in (101.6 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

