



## Main

Range	9080FB
Product	Fuse holder

## Complementary

Current Rating	60 A
[Ue] rated operational voltage	<= 250 V AC/DC
Fuse type	R
Fuse size	0.8125 x 3 in
Number of poles	1
Electrical connection	Box lugs
Wire Gauge	AWG 14...AWG 2 copper or aluminium
SCCR	200 kA UL 512
Product certifications	CE UL listed file E40747 CCN IZLT CSA file 70360 class 6225 01
Operating Temperature	-40...257 °F (-40...125 °C)
Mounting Type	Surface mount
Block Material	Thermoplastic block
Wire stripping length	0.5625 in (14.29 mm)
Terminal Tightening Torque	Lugs 50 lbf.in (5.65 N.m) AWG 3...AWG 2 copper or aluminium Lugs 45 lbf.in (5.08 N.m) AWG 6...AWG 4 copper or aluminium Lugs 40 lbf.in (4.52 N.m) AWG 8 copper or aluminium Lugs 35 lbf.in (3.95 N.m) AWG 12...AWG10 copper or aluminium Lugs 35 lbf.in (3.95 N.m) AWG 14 copper
Height	4.83 in (122.68 mm)
Width	1.48 in (37.59 mm)
Depth	2.01 in (51.05 mm)

## Ordering and shipping details

Category	21701 - 9080 FB
Discount Schedule	CP1
GTIN	00785901097808
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.00 in (5.08 cm)
Package 1 width	1.50 in (3.81 cm)
Package 1 Length	4.80 in (12.192 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	50
Package 2 Weight	11.50 lb(US) (5.216 kg)
Package 2 Height	5.70 in (14.478 cm)
Package 2 width	10.70 in (27.178 cm)
Package 2 Length	17.00 in (43.18 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------