



Main

Range	9080FB
Product	Fuse holder

Complementary

Current Rating	30 A
[Ue] rated operational voltage	<= 600 V AC/DC
Fuse type	J
Fuse size	0.8125 x 2.25 in
Number of poles	3
Electrical connection	Box lugs
Wire Gauge	AWG 14...AWG 2 copper or aluminium
SCCR	200 kA UL 512
Product certifications	CSA file 70360 class 6225 01 CE UL listed file E40747 CCN IZLT
Operating Temperature	-40...257 °F (-40...125 °C)
Mounting Type	Surface mount
Block Material	Thermoplastic block
Wire stripping length	0.4375 in (11.11 mm)
Terminal Tightening Torque	Screw terminals 25 lbf.in (2.82 N.m) AWG 14...AWG 6 copper
Height	4.07 in (103.38 mm)
Width	4.72 in (119.89 mm)
Depth	2.09 in (53.09 mm)

Ordering and shipping details

Category	21701 - 9080 FB
Discount Schedule	CP1
GTIN	00785901139638
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.00 in (5.08 cm)
Package 1 width	3.30 in (8.382 cm)
Package 1 Length	3.40 in (8.636 cm)
Unit Type of Package 2	CAR

Number of Units in Package 2	20
Package 2 Weight	8.01 lb(US) (3.633 kg)
Package 2 Height	4.40 in (11.176 cm)
Package 2 width	9.90 in (25.146 cm)
Package 2 Length	17.50 in (44.45 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------