



### Main

|                                    |                              |
|------------------------------------|------------------------------|
| Range                              | Thalassa                     |
| Accessory / separate part category | Mounting accessory           |
| Product or component type          | Mounting plate               |
| Device application                 | Multi-purpose                |
| Enclosure nominal dimensions       | -                            |
| Mounting location                  | Step slide<br>Back inserts   |
| Mounting plate description         | Plain                        |
| Range compatibility                | Thalassa PLA<br>Thalassa PHD |
| Device composition                 | 1 mounting plate             |
| Material                           | Galvanised steel             |

### Complementary

|                            |   |
|----------------------------|---|
| Fixing mode                | By screws M8 - on back inserts                        |
| Permanent permissible load | 330.69 lb(US) (150 kg)                                |
| Height                     | Nominal 49.21 in (1250 mm)<br>Real 44.88 in (1140 mm) |
| Width                      | Nominal 49.21 in (1250 mm)<br>Real 44.29 in (1125 mm) |
| Depth                      | Real 4.92 in (125 mm)                                 |
| Thickness                  | 0.98 in (25 mm)                                       |

### Ordering and shipping details

|                       |                                       |
|-----------------------|---------------------------------------|
| Category              | 80036 - ENCLOSURE SYSTEMS ACCESSORIES |
| Discount Schedule     | ES1                                   |
| GTIN                  | 00785901342755                        |
| Nbr. of units in pkg. | 1                                     |
| Package weight(Lbs)   | 53.44 lb(US) (24.24 kg)               |
| Returnability         | Yes                                   |
| Country of origin     | ES                                    |

### Packing Units

|                  |                        |
|------------------|------------------------|
| Package 1 Height | 0.59 in (15.000 mm)    |
| Package 1 width  | 44.49 in (1130.000 mm) |
| Package 1 Length | 44.49 in (1130.000 mm) |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| REACH Regulation           | <a href="#">REACH Declaration</a>  |
| REACH free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|