

Tilt Wall Mount for 26" to 55" TVs and Monitors, -10° to 0° Tilt

MODEL NUMBER: DWT2655XE



Low-profile mount hangs a flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. -10° to 0° tilt capability for optimal viewing angles.

Description

The VESA-compliant DWT2655XE Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 26 to 55 inches. A -10° to 0° tilt capability minimizes glare and provides comfortable viewing from multiple angles.

Low-profile mount is concealed behind the display to give a sleek, professional appearance. Frame is open for easy wall access. Mounting rails adjust horizontally to compensate for off-center wall studs. Built-in bubble level allows accurate display leveling. Durable all-metal frame with scratch-resistant powder-coated finish supports up to 165 lbs (74.8 kgs). Mounting hardware included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 100 x 100 mm, 100 x 200 mm, 200 x 100 mm, 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm and 400 x 400 mm.

Features

Mounts Your TV or Monitor to the Wall Fits most flat-panel televisions, monitors and other displays from 26 to 55 in. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Mounts out of sight behind display for sleek, professional appearance. Mounting hardware included.

Convenient One-Touch Adjustment -10° to 0° tilt capability provides comfortable viewing from multiple angles. Improves viewing angles in applications where audience is below the display.

Durable Metal Construction Supports up to 165 lbs (74.8 kgs). Open frame allows easy wall access. Adjustable mounting rails compensate for off-center wall studs. Built-in bubble level for accurate display leveling. Scratch-resistant powder-coated finish.

VESA Compliance Supports the following VESA mounting hole patterns: 100 x 100 mm, 100 x 200 mm, 200 x 100 mm, 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm and 400 x 400 mm.

Specifications

Highlights

- Fits most flat-panel displays from 26 to 55 in.
- Hangs out of sight for a sleek, professional appearance
- -10° to 0° tilt capability provides comfortable viewing
- Supports up to 165 lbs (74.8 kgs)

Package Includes

- DWT2655XE Tilt Wall Mount for 26" to 55" TVs and Monitors
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 20 screws
- (4) M8 x 30 screws
- (4) Washers
- (8) Small spacers
- (4) Big spacers
- (6) Anchor bolts
- (6) Concrete anchors
- (6) D6 washers
- Owner's manual



OVERVIEW	
UPC Code	037332183583
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x200; 200x100; 200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400
Motion	Tilt
Mounting Location	Wall
Degrees of Motion	-10/+0 Tilt
Distance from Wall (in.)	1.77
Distance from Wall (cm)	5
Distance from Wall (mm)	45
Minimum Screen Size (in.)	26
Maximum Screen Size (cm)	139.7
Maximum Screen Size (in.)	55
Minimum Screen Size (cm)	66.04
Maximum Weight Capacity (lbs.)	165
Maximum Weight Capacity (kg)	75
Number of Displays	1
Shipping Dimensions (hwd / cm)	5.51 x 21.49 x 49.00
Shipping Dimensions (hwd / in.)	2.17 x 8.46 x 19.29
Shipping Weight (kg)	2.40
Shipping Weight (lbs.)	5.30
Unit Dimensions (hwd / cm)	20.3 x 46.4 x 4.77
Unit Dimensions (hwd / in.)	7.99 x 18.27 x 1.48
Unit Weight (kg)	2.79
Unit Weight (lbs.)	6.16
FEATURES & SPECIFICATIONS	
Cord Management	No
Tools Necessary	Yes
Security Lock	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

STANDARDS & COMPLIANCE	
Approvals	RoHS3, REACH
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>