

In most applications, a signal booster (Model Number: B120-000-SL) should be used with this cable to ensure a signal strong enough for your display. An alternate solution is to use a Tripp Lite DVI over Cat5 Extender (Model Number: B140-101X) in place of a 50 ft. DVI cable and signal booster.

DVI Single Link Easy Pull Digital TMDS Monitor Cable (DVI-D M/M), 50 ft. (15.24 m)

MODEL NUMBER: P561-050-EZ



Description

Tripp Lite's 50-ft. (15.24 m) DVI-D Single Link Easy Pull All-in-One Monitor Cable makes running long length video cables a snap. The pull-apart design allows the cable to be run through conduit or other tight areas that a DVI connector wouldn't fit through. Diameter of the circular DIN end is only 7/8". Circular Easy Pull connector is threaded to ensure maximum security once the cable is reattached. Use in conjunction with DVI video cards that are specified as Single Link. DVI connectors are molded, have integral strain relief for long life reliability, and a ferrite collar to drain off extraneous electrical interference. In most applications, a signal booster (B120-000-SL) will need to be used with this cable to ensure a signal strong enough for your display.

Features

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- For use with Single Link TMDS specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 1920 x 1200
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- In most applications, a signal booster (B120-000-SL) will need to be used with this cable to ensure a signal strong enough for your display

Highlights

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- For use with Single Link TMDS specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 1920 x 1200
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

Package Includes

- 50-ft. (15.24 m) Easy Pull All-in-One DVI Single Link Cable (DVI-D M/M)



Specifications

OVERVIEW	
UPC Code	037332142290
Technology	DVI
PHYSICAL	
Color	Black
Cable Length (ft.)	50
Cable Length (m)	15.2
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 2.54
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 1.00
Shipping Weight (kg)	1.27
Shipping Weight (lbs.)	2.80
CONNECTIONS	
Side A - Connector 1	DVI-D SINGLE LINK (MALE)
Side B - Connector 1	DVI-D SINGLE LINK (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>