



Main

Product or component type	Mechanically Held Lighting Contactor
Range of product	8903LX
Control Circuit	Separate control circuit

Complementary

Control Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Inrush power in VA	140 VA 60 Hz 150 VA 50 Hz 180 VA 50/60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	4P 4 NO
Control Unit	No control units
Pilot Light	No indicator
Other Options	2P relay (1 NO + 1 NC)
Electrical connection	Screw-clamp terminals
Height	12.68 in (322 mm)
Depth	6.02 in (153 mm)
Width	7.80 in (198 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product certifications	UL Listed CSA

Ordering and shipping details

Category	21322 - 8903 LX (NOT L)
Discount Schedule	CP1
GTIN	00785901023289
Nbr. of units in pkg.	1
Package weight(Lbs)	11.23 lb(US) (5.09 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	7.70 in (19.558 cm)
Package 1 width	8.20 in (20.828 cm)
Package 1 Length	13.00 in (33.020 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------