

# Product data sheet

## Characteristics

# NSYAMPM2419TB

Mounting plate in galvanized steel, thickness 1.5 mm For boxes of H225W175 mm



### Main

Range	Thalassa
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Device application	Multi-purpose
Enclosure nominal dimensions	-
Mounting location	Back studs
Mounting plate description	Plain
Range compatibility	Thalassa TBS Thalassa TBP
Device composition	1 mounting plate
Material	Galvanised steel

### Complementary

Fixing mode	By screws M4 self tapping - on back studs
Height	Nominal 9.49 in (241 mm) Real 66.34 in (1685 mm)
Width	Nominal 7.64 in (194 mm) Real 8.46 in (215 mm)
Thickness	0.06 in (1.5 mm)
Net Weight	0.26 lb(US) (0.12 kg)



### Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	00785901946656
Nbr. of units in pkg.	1
Package weight(Lbs)	2.2 lb(US) (1.00 kg)
Returnability	No
Country of origin	FR

### Packing Units

Package 1 Height	0.08 in (2.000 mm)
Package 1 width	6.69 in (170.000 mm)
Package 1 Length	8.46 in (215.000 mm)

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes

---

RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---