



Main

| | |
|------------------------------------|--|
| Range | Spacial |
| Accessory / separate part category | Mounting accessory |
| Product or component type | Mounting plate |
| Device application | Multi-purpose |
| Enclosure nominal dimensions | 15.75 in (400 mm) 11.81 in (300 mm) 11.81 in (300 mm) 15.75 in (400 mm) |
| Mounting location | Step slide Direct fixing on backstuds |
| Mounting plate description | Plain |
| Range compatibility | Spacial S3D Spacial CRN Spacial S3X Thalassa PLM |
| Quantity per set | Set of 1 |
| Material | Galvanised steel |

Complementary

| | |
|----------------------------|---|
| Fixing mode | Screwed on backstuds M8 By fixing element |
| Permanent permissible load | 132.28 lb(US) (60 kg) |
| Height | 13.78 in (350 mm) |
| Width | 9.84 in (250 mm) |
| Depth | 4.92 in (125 mm) |
| Thickness | 0.07 in (1.8 mm) |
| Net Weight | 2.82 lb(US) (1.28 kg) |
| Variant particularity | Installation in enclosures with inverted dimensions |

Ordering and shipping details

| | |
|-----------------------|---------------------------------------|
| Category | 80036 - ENCLOSURE SYSTEMS ACCESSORIES |
| Discount Schedule | ES1 |
| GTIN | 00785901646570 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 2.73 lb(US) (1.24 kg) |
| Returnability | Yes |
| Country of origin | ES |

Packing Units

| | |
|------------------|-----------------------|
| Package 1 Height | 13.78 in (350.000 mm) |
| Package 1 width | 9.84 in (250.000 mm) |
| Package 1 Length | 0.20 in (5.000 mm) |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|