

AC50

14 MIL PREMIUM DUCT TAPE

DESCRIPTION

Polyethylene (PE) coated cloth tape with aggressive pressure sensitive natural rubber adhesive. Specifically designed for applications where a significant level of tensile and tear strength is required. An excellent choice for sealing heating and air ventilation systems, repairs, and serves as an excellent moisture barrier.

PRODUCT APPLICATION

HVAC Applications, asbestos/lead/fiberglass abatement, sand blasting.

GOVERNMENT COMPLIANCE

Meets HUD, BOCA, and L.A. County codes. Tested in accordance with UL-723.

ASTM D5486, Type IV
PPP-T-60, Type IV, Class 1
Ford Motor ESB M3G58-A

STORAGE RECOMMENDATION

Store new stock behind current stock. Store in a clean, dry place. Temperature of 70°F (21°C) +/- 6°F, and 40% to 50% relative humidity are recommended.

SHELF LIFE

When stored under recommended conditions, converted rolls have an expected shelf life of up to one year from date of shipment. Jumbo rolls have the same expected shelf life but it is recommended that they are converted within 6 months of date of shipment.



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA

Customer Service: 800.IPG.8273 | 800.474.8273

Tape Technical Service: 877.447.4832

www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 03/20

INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

NOMINAL VALUES

The following data are nominal values based on PSTC, ASTM and other standard tests. The data should not be considered as specifications.

Backing	PE Film
Adhesive	Natural Rubber/Resin
Reinforcement	PET Cloth
Adhesion to Steel (oz/in of width) PSTC-101	44 (12.0 N/25mm)
Tensile Strength (lbs/in of width) PSTC-131	42 (184 N/25mm)
Elongation (% at break) PSTC-131	21
Total Thickness (mils) PSTC-133	14 (0.356mm)
Colors	Silver, Black, White, Olive Drab Green
Application Temperature Range	+40°F ~ +90°F (+4°C ~ +32°C)
Operational Temperature Range	+32°F ~ +200°F (0°C ~ +93°C)

