



Main

Product	Surface cover
Color	Gray
Cover type	Surface cover
Type of front plate	Ventilated Hinged

Complementary

Material	Steel
Height	74 in (1879.60 mm)
Width	20 in (508.00 mm)
Tightening torque	Cover 10...12 lb.in

Environment

Enclosure Rating	NEMA 1
Product certifications	CULus

Ordering and shipping details

Category	08352 - NF / NQ TRIMS RTA
Discount Schedule	PE1A
GTIN	00785901003922
Nbr. of units in pkg.	1
Package weight(Lbs)	42 lb(US) (19.05 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	0.15 ft (0.046 m)
Package 1 width	1.83 ft (0.559 m)
Package 1 Length	6.61 ft (2.014 m)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------