

HC2886WP

HCP-SU 26 INCH WIDE by 86 INCH HIGH TYPE3R/12 I-LINE PANELBOARD ENCLOSURE



Main

Range of product	I-Line
Product or component type	Enclosure
Device application	Panelboard
Device short name	HCP-SU

Complementary

Line Rated Current	800 A
Enclosure nominal width	25.98 in (660 mm)
Enclosure nominal height	85.98 in (2184 mm)
Enclosure nominal depth	9.49 in (241 mm)
Net Weight	352.74 lb(US) (160 kg)
Height	87 in (2209.80 mm)
Depth	14 in (355.60 mm)

Environment

NEMA degree of protection	NEMA 3R/12
Standards	CSA UL

Ordering and shipping details

Category	00110-RTA PB BOX - SPL, 3R, ETC.
Discount Schedule	PE1A
GTIN	00785901231387
Package weight(Lbs)	352.00 lb(US) (159.665 kg)
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------
