



Main

Product	Double Throw Safety Switch
Duty Rating	General duty
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	None
Number of Poles	3
Current Rating	30 A
Voltage Rating	240 V AC
Enclosure Rating	NEMA 1

Complementary

Short-circuit current	10 kA H or K
Fuse type	H or K
Mounting Type	Surface
Wire Size	AWG 12...AWG 2 aluminium AWG 14...AWG 2 copper
Tightening torque	35 Lbf.In (3.95 N.m) 0.00...0.01 in ² (2.08...5.26 mm ²) (AWG 14...AWG 10) 40 Lbf.In (4.52 N.m) 0.01 in ² (8.37 mm ²) (AWG 8) 45 Lbf.In (5.08 N.m) 0.02...0.03 in ² (13.3...21.15 mm ²) (AWG 6...AWG 4) 50 lbf.in (5.65 N.m) 0.04...0.05 in ² (26.67...33.62 mm ²) (AWG 3...AWG 2)
Depth	4.75 in (120.65 mm)
Width	9.75 in (247.65 mm)
Height	10 in (254.00 mm)
Net Weight	8.00 lb(US) (3.63 kg)

Environment

Certifications	UL Listed
----------------	-----------

Ordering and shipping details

Category	00033 - DT SWITCH,NEMA1
Discount Schedule	DE1
GTIN	00785901454588
Nbr. of units in pkg.	1
Package weight(Lbs)	8.82 lb(US) (4.00 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	5.00 in (12.700 cm)
Package 1 width	10.10 in (25.654 cm)
Package 1 Length	11.00 in (27.940 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------