



Main

Product Type	Sub-feed lug
Marketing Trade Name	QO
Rated Current	125 A
Number of Spaces	2
Number of Phases	2 phases
Voltage Rating	240 V AC

Complementary

Number of Poles	2
Wire Size	AWG 12...AWG 2/0 copper or aluminium
Product Certifications	CSA CURus
Mounting Mode	Bolt-on
Height	3.500 in (88.90 mm)
Width	1.494 in (37.95 mm)
Depth	2.310 in (58.67 mm)

Environment

Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
---------------------------------------	---------------------------------

Ordering and shipping details

Category	00015 - QOB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901031352
Nbr. of units in pkg.	1
Package weight(Lbs)	0.61 lb(US) (0.28 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	3.50 in (8.890 cm)
Package 1 width	4.00 in (10.160 cm)
Package 1 Length	1.80 in (4.572 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------