

Product data sheet

Characteristics

9422ATDN601

Operating mechanism, flange mounted, variable depth, 60A, 600 V, no fuse, switch mechanism, 6 inch handle, NEMA 4



Main

Range	9422T
Product	Disconnect Switch
Disconnect Type	Non-fusible disconnect switch

Complementary

Mounting Type	Flange rod variable depth
Current Rating	60 A
Horsepower Rating	15 Hp 200 V AC 15 Hp 230 V AC 30 Hp 460 V AC 50 Hp 575 V AC 10 hp 250 V DC
Handle Type	6 in handle included NEMA 1/3/3R/4 enclosures sheet steel

Environment

Certifications	CSA UL Recognized
----------------	----------------------

Ordering and shipping details

Category	21732 - 9422
Discount Schedule	CP1
GTIN	00785901872177
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	7.10 in (18.034 cm)
Package 1 width	11.30 in (28.702 cm)
Package 1 Length	16.00 in (40.640 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------