

# Product data sheet

## Characteristics

# QMB361T

Fusible Switch, QMB, 30 A to 30 A, 600 VAC, 3 pole, 3 hp, 4.5 in



### Main

Product or component type	Fuse-switch
Range of product	Square D QMB

### Complementary

Line Rated Current	30 A
Device mounting	Surface
Height	4.5 in (114.30 mm)
Material	Steel
Number of poles	3
Rated Voltage	600 V AC
Product destination	Meter board Distribution board
Protection type	Fuse protection
Short-circuit protection	200000 A AIR
Switch function	TPST
Wiring configuration	Without neutral

### Environment

Product certifications	UL Listed
------------------------	-----------

### Ordering and shipping details

Category	00037 - QMB BRANCH CB,SW,& MAIN SW
Discount Schedule	PE1A
GTIN	00785901535898
Nbr. of units in pkg.	1
Package weight(Lbs)	17.63 lb(US) (8.00 kg)
Returnability	Yes
Country of origin	US

### Packing Units

Package 1 Height	5.10 in (12.954 cm)
Package 1 width	12.30 in (31.242 cm)
Package 1 Length	25.50 in (64.770 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------