

Product data sheet

Characteristics

KAG3H

operating head 45 x 45 mm - black color - black handle - blank for engraving



Main

Range of product	Harmony Series K
Product or component type	Cam switch operating head
Component name	KAG
Product compatibility	Front mounting bodies 12 and 20 A by multifixing
Cam switch head type	With front plate 45 x 45 mm
Type of operator	Black handle 1.38 in (35 mm)
Rotary handle padlocking	Without
Presentation of legend	With mat black

Complementary

Mechanical durability	1000000 cycles
CAD overall width	1.77 in (45 mm)
CAD overall height	1.77 in (45 mm)
CAD overall depth	1.34 in (34 mm)
Length	1.38 in (35 mm)
Net Weight	0.03 lb(US) (0.012 kg)
Compatibility code	KAG

Environment

Protective treatment	TC
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Shock resistance	30 gn conforming to IEC 68-2-27
Vibration resistance	5 gn 10...150 Hz)IEC 68-2-6
IP degree of protection	IP40 conforming to IEC 529 IP40 conforming to NF C 20-010

Ordering and shipping details

Category	18402 - WORLD SERVICE PARTS(CONTROL ACCESS)
Discount Schedule	CP10
GTIN	03389110980448
Nbr. of units in pkg.	1
Package weight(Lbs)	0.03 lb(US) (0.01 kg)
Returnability	No
Country of origin	CZ

Packing Units

Package 1 Height	0.250 dm
Package 1 width	0.900 dm
Package 1 Length	0.900 dm

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------