

Product data sheet

Characteristics

2510FG6P

Manual Starter, fractional horsepower, 16A, 2 poles, 1 HP at 277 VAC, toggle w/guard, red indicator, NEMA 1 enclosure



Main

| | |
|---------------------|----------------------------|
| Product | Single Unit Manual Starter |
| Type | F |
| Overload Relay Type | Melting alloy |

Complementary

| | |
|-----------------------|---|
| Current Rating | 16 A |
| Cable entry | 0.5" and 0.75" knock-outs (top and bottom) |
| Horsepower Rating | 1 Hp 115 V AC 1 Hp 277 V AC 0.75 Hp 115 V DC 0.75 Hp 230 V DC 2 hp 230 V AC |
| Voltage Rating | 277 V AC 230 V DC |
| Number of Poles | 2P |
| Control Unit | Toggle switch (with lock-off) |
| Number of Phases | 1 phase |
| Pilot Light | Red indicator |
| Reset | Manual |
| Motor starter type | Non reversing |
| Electrical connection | Screw clamp terminals |
| Wire Gauge | AWG 14...AWG 12 copper |
| Height | 4.25 in (107.95 mm) |
| Width | 2.44 in (61.98 mm) |
| Depth | 2.88 in (73.15 mm) |

Environment

| | |
|------------------------|---|
| Product certifications | UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05 |
| NEMA Enclosure Rating | NEMA 1 Plastic standard size |

Ordering and shipping details

| | |
|-----------------------|--------------------------|
| Category | 21101 - 2510,2511,2512 F |
| Discount Schedule | CP1 |
| GTIN | 00785901554042 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.84 lb(US) (0.38 kg) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------|---------------------|
| Package 1 Height | 3.00 in (7.620 cm) |
| Package 1 width | 4.70 in (11.938 cm) |
| Package 1 Length | 2.60 in (6.604 cm) |

Offer Sustainability

| | |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Not compliant |
| China RoHS Regulation | China RoHS Declaration |
| PVC free | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Approximate Dimensions

