



Main

Product Range	Type S
Component type	Auxiliary Contact Module
Used with	Contactors starter

Complementary

NEMA size	1 6 7 5 0 3 2 00 4
Auxiliary contact composition	1 NO
[Uc] control circuit voltage	<= 600 V AC 50/60 Hz
Rated breaking capacity	6 A 120 V AC inductive control circuit UL 508 3 A 240 V AC inductive control circuit UL 508 1.2 A 600 V AC inductive control circuit UL 508 1.5 A 480 V AC inductive control circuit UL 508 10 A <= 600 V AC resistive control circuit UL 508

Environment

Product certifications	UL Listed CSA UL Recognized
------------------------	-----------------------------------


Ordering and shipping details

Category	21761 - 9999 DISCOUNT CP1
Discount Schedule	CP1
GTIN	00785901721307
Nbr. of units in pkg.	1
Package weight(Lbs)	0.17 lb(US) (0.08 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	1.50 in (3.810 cm)
Package 1 width	3.00 in (7.620 cm)
Package 1 Length	4.50 in (11.430 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------