



## Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Type of filter	Standard
Flow rate	Free flow rate with standard filter 43589.17 Gal/hr(US) (165 m <sup>3</sup> /h) 50 Hz Free flow rate with standard filter 50986.12 Gal/hr(US) (193 m <sup>3</sup> /h) 60 Hz
[Us] rated supply voltage	175...253 V
Input voltage	230 V 50/60 Hz

## Complementary

Absorbed power	16.3 W 50 Hz 14.3 W 60 Hz
Line Rated Current	0.12 A 50 Hz 0.94 A 60 Hz
Noise level < at	50...51 dB
Bearing type	Ball
Height	External 10.55 in (268 mm)
Width	External 9.76 in (248 mm)
Depth	External 4.09 in (104 mm)
Cut-out dimensions	223 x 223 mm
Net Weight	2.51 lb(US) (1.14 kg)
Material	Outlet grille injected thermoplastic (ASA PC)
Color	Outlet grille: grey (RAL 7035)
Ambient air temperature for operation	-4...140 °F (-20...60 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Maximum pressure	50 Pa flow rate 0 m <sup>3</sup> /h
Connections - terminals	Faston connector
IP degree of protection	IP54
Device composition	1 axial motor 2 protective grille on the front and rear surfaces 1 filter front of axial motor 1 outlet grille front 1 cut-out template 1 power cord
Condition of use	Overfrequent filter replacement should be avoided Filter must be cleaned and replaced regularly Flow rates depends on the work point, see ProClima software Outside temperature must be 5 °C lower than inside temperature Surrounding environment must be relatively clean

## Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	00785901698494
Nbr. of units in pkg.	1
Package weight(Lbs)	3.22 lb(US) (1.46 kg)
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	7.48 in (19 cm)
Package 1 width	9.84 in (25 cm)
Package 1 Length	10.63 in (27 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------