

# 4-Port USB over Cat5 Hub with 4 Remote Ports, TAA

MODEL NUMBER: **U224-4R4-R**



## Description

Tripp Lite's 4-Port USB 1.1 over Cat5 extender hub allows USB peripherals to be located up to 150-ft. (45.72 m) from your computer. Simply plug the transmitter into the USB port on your computer, connect your USB peripherals, and run Cat5e/Cat6 cable up to 150-ft. (45.72 m) to the remote receiver unit and connected devices. Plug-and-play; no software or drivers required. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

## Features

- Locate 4 USB 1.1 peripherals up to 150-ft. (45.72 m) from your computer
- Uses readily available Cat5e/Cat6 patch cable
- Plug-and-play; no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Highlights

- Locate 4 USB 1.1 peripherals up to 150-ft. (45.72 m) from your computer
- Uses readily available Cat5e/Cat6 patch cable
- Plug-and-play; no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Package Includes

- Local transmitter unit
- 4-Port remote receiver unit
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 4.5 ft.)
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332146687
Product Type	Hub
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 4.5 ft.
Technology	USB 2.0 (High Speed); USB
Host Connector	USB A (MALE)
VIDEO	



Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
<b>DATA</b>	
Data Ports	(4) USB A (FEMALE)
Data Ports Detail	(4) USB-A - USB 2.0
<b>INPUT</b>	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 1-15P North America
<b>POWER</b>	
External Power Supply Input Specs (V / Hz / A)	100-240V, 50/60Hz, 0.35A
External Power Supply Output Specs (V / A)	5V, 2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.5
External Power Supply DC Barrel Connector Specs	OD: 3.5 x 1.35 x 8mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	CE; FCC; UL
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Red - Connection; Green - Activity
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Plastic
Receiver Unit Height (in.)	0.9
Receiver Unit Width (in.)	2.4
Receiver Unit Depth (in.)	3.3
Shipping Dimensions (hwd / cm)	5.84 x 22.61 x 14.99
Shipping Dimensions (hwd / in.)	2.30 x 8.90 x 5.90
Shipping Weight (kg)	0.34
Shipping Weight (lbs.)	0.75
Transmitter Unit Depth (in.)	2.6
Transmitter Unit Height (in.)	0.9



Transmitter Unit Width (in.)	1.8
<b>CONNECTIONS</b>	
Ports	4
Side A - Connector 1	USB A (MALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	(4) USB A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>