



Main

Product	Single Throw Safety Switch
Duty Rating	General duty
Device application	Residential
Disconnect Type	Non-fusible disconnect switch
Factory Installed Neutral	None
Phase	3 phase
Number of Poles	3
Current Rating	30 A
Voltage Rating	240 V AC
Enclosure Rating NEMA	NEMA 1
Maximum Horse Power Rating	150 hp 240 V at AC 60 Hz for 3 phase conforming to NEC 430.52

Complementary

Mounting Type	Surface
Electrical Connection	Lugs
Wiring configuration	3-wire
Wire Size	AWG 4...500 kcmil aluminium/copper
Tightening torque	450 lbf.in (50.84 N.m) (AWG 4...500 kcmil)
Depth	8.88 in (225.55 mm)
Width	24.88 in (631.95 mm)
Height	45.12 in (1146.05 mm)
Net Weight	117.07 lb(US) (53.1 kg)

Environment

Certifications	UL listed file E2875
----------------	----------------------

Ordering and shipping details

Category	00007 - D & DU SW, NEMA1, 400-600A
Discount Schedule	DE1A
GTIN	00785901461630
Nbr. of units in pkg.	1
Package weight(Lbs)	117 lb(US) (53.07 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	10.98 in (27.9 cm)
Package 1 width	30.00 in (76.2 cm)
Package 1 Length	50.00 in (127 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------