



Main

Product or component type	Circuit breaker
---------------------------	-----------------

Complementary

Number of Poles	3P
Breaking capacity code	D
Magnetic hold current	1000 A
Magnetic tripping current	2000 A
Electrical connection	Lugs line Terminal nut load
Tightening torque	230.12 lbf.in (26 N.m) 0.15...0.29 in ² (95...185 mm ²) (AWG 3/0...350 kcmil)
Height	7.52 in (191.01 mm)
Width	4.12 in (104.65 mm)
Depth	5 in (127.00 mm)
Continuous current rating	80 %

Ordering and shipping details

Category	01110 - HD,JD UNIT MT BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901946854
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Circularity Profile	End Of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------
